





SCALE= 0.250









NOTES
1. QC. DIM BE SPECIFIED AS (1)~(3)
2. ALL PARTS ARE ROHS COMPLIANT
3.TEXTURED SURFACES ON OUTSIDE: ??

Reason			UNSPECIFIED TOL'S (± 0.2 mm)							FINISH.	Accton TECHNOLOGY CORP.		
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.			ANGLE ±1°	DIM. \ GRADE	0	1	2	3	4	5	WHITE		
			ROUGHNESS	0 — 16	0.05	0.1	0.15	0.2	0.2	0.5	PART NO. 123100000887A	SCALE 1 / 1 UNIT MM [IN]	
				16 — 63	0.05	0.15	0.2	0.3	0.3	0.8		DESIGN Yvonne 07/11'16	DWG. TITLE BASE EAP1018B
				63 — 250	0.05	0.2	0.25	0.4	0.5	1.2	MATERIAL Cycoloy CX7240, UL=94, V0 VERDER:SABIC		SHEET 1 / 1
				250 — 500	0.1	0.25	0.3	0.6	0.8	1.8			REV. A1
ZONE		DESCRIPTION		500 — 1000		0.3	0.5	0.8	1.2	3.0			SIZE A3