






| Reason                                                                                                                                                                               |                                   |  |                | UNSPECIFIED TOL'S ( ± 0.2 mm ) |       |      |      |      |     |     |     |          |                          |  FINISH. |          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|--|----------------|--------------------------------|-------|------|------|------|-----|-----|-----|----------|--------------------------|-----------------------------------------------------------------------------------------------|----------|
| This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission. |                                   |  | ANGLE<br>± 1 ° | DIM.                           | GRADE | 0    | 1    | 2    | 3   | 4   | 5   | PART NO. |                          |                                                                                               |          |
|                                                                                                                                                                                      |                                   |  |                | 0                              | 16    | 0.05 | 0.1  | 0.15 | 0.2 | 0.2 | 0.5 |          |                          |                                                                                               |          |
|                                                                                                                                                                                      |                                   |  | ROUGHNESS      | 16                             | 63    | 0.05 | 0.15 | 0.2  | 0.3 | 0.3 | 0.8 |          |                          |                                                                                               |          |
|                                                                                                                                                                                      |                                   |  |                | 63                             | 250   | 0.05 | 0.2  | 0.25 | 0.4 | 0.5 | 1.2 |          |                          |                                                                                               |          |
|                                                                                                                                                                                      |                                   |  |                | 250                            | 500   | 0.1  | 0.25 | 0.3  | 0.6 | 0.8 | 1.8 |          |                          |                                                                                               |          |
| A7                                                                                                                                                                                   | MOVIE THE ANTENNA IPEX CONNECTOR. |  |                |                                |       |      |      |      |     |     |     | MATERIAL | SCALE 1 / 2 UNIT MM (IN) |                                                                                               |          |
|                                                                                                                                                                                      |                                   |  |                |                                |       |      |      |      |     |     |     |          | DESIGN                   | Yvonne                                                                                        | 05/26/16 |
| ZONE                                                                                                                                                                                 | DESCRIPTION                       |  |                |                                |       |      |      |      |     |     |     | PCB      | t=1.6mm ±10%             |                                                                                               |          |
|                                                                                                                                                                                      |                                   |  |                | 500                            | 1000  |      | 0.3  | 0.5  | 0.8 | 1.2 | 3.0 |          |                          |                                                                                               |          |

Accton

TECHNOLOGY CORP.

|                        |  |            |  |      |      |
|------------------------|--|------------|--|------|------|
| DWG. TITLE             |  | SHEET 1/ 1 |  | REV. | SIZE |
| PCB AP1024A-V2-1215-ZZ |  | A7         |  | A3   |      |