



FMA-MD01001-02 R02






SCALE: 0.500







NOTE
1.Dimensions (1)~(3) are IQC checkpoints.
2.All material should match RoHS request.

Reason		
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.		
	ZONE	DESCRIPTION

UNSPECIFIED TOL'S (± 0.2 mm)

ANGLE ±1 °

ROUGHNESS

DIM. \ GRADE	0	1	2	3	4	5
0 — 16	0.05	0.1	0.15	0.2	0.2	0.3
16 — 63	0.05	0.15	0.2	0.3	0.3	0.8
63 — 250	0.05	0.2	0.25	0.4	0.5	1.2
250 — 500	0.1	0.25	0.3	0.6	0.8	1.8
500 — 1000		0.3	0.5	0.8	1.2	3.0

FINISH.
COATING:PANTONE COOL GRAY 1

PART NO.
123400001193A

SCALE 1 / 1 | UNIT MM (IN)

DESIGN | Yvonne | 12/10'15

MATERIAL
SUS 304 , t=3mm

Accton TECHNOLOGY CORP.

DWG. TITLE
POLE-MOUNT DAP1122B

SHEET 1 / 1

REV. 01

SIZE A3