



FMA-MD01001-02 R02



SCALE: 0.250







NOTE
1.Dimensions (1)~(3) are IQC checkpoints.
2.All material should match RoHS request.

Reason											
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.			UNSPECIFIED TOL'S (± 0.2 mm)								
			ANGLE ±1°	DIM. \ GRADE	0	1	2	3	4	5
			ROUGHNESS	0 — 16	0.05	0.1	0.15	0.2	0.2	0.3
				16 — 63	0.05	0.15	0.2	0.3	0.3	0.8
				63 — 250	0.05	0.2	0.25	0.4	0.5	1.2
				250 — 500	0.1	0.25	0.3	0.6	0.8	1.8
				500 — 1000		0.3	0.5	0.8	1.2	3.0
	ZONE	DESCRIPTION								

FINISH: NO COATING

PART NO. 123700000098A | SCALE 1 / 2 | UNIT MM [IN] | DESIGN Yvonne 02/15'16

MATERIAL: AL 5052 , t=1mm

Accton TECHNOLOGY CORP.

DWG. TITLE: REFLECTOR DAP1122B | SHEET 1 / 1 | REV. 01 | SIZE A3