



PART NUMBER
OCP Surrogate Base Light


REV	CHG NO	DESCRIPTION	DATE











EPDM
STATE:
TIME:
DATE:
VERSION:

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES			
TOLERANCES:			
4 PLACE	3 PLACE	2 PLACE	ANGLES
±.0005	±.005	±.01	±1°

THIRD ANGLE PROJECTION		MATERIAL: 6061-T6 ALUMINUM
CORNERS EDGES BROKEN	OUTSIDE: .010 MAX	FINISH:
	INSIDE: .010 MAX	
WORKMANSHIP PER: N/A	SCALE: 1:1	

DWN			
CHK			
ENG			
MFG			
QA			

TITLE: OCP Acoustic Surrogate Base Light

DRAWING NUMBER: D750351650 REV: A01

D

SHEET: 1 OF 1

FORMAT NO. 1040-1,2M REV E