

8		7		6		5		4		3		2		1		
PART NUMBER												REV	CHG NO	DESCRIPTION		DATE
750351800																

F

F

E

E

D

D

C




C

B

B

A

A



EPDM		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER				THIRD ANGLE PROJECTION		MATERIAL:		DWN		TITLE: OCP Acoustic Surrogate Bottom Cover		DRAWING NUMBER		REV	
STATE: TIME: DATE: VERSION:						6061-T6 ALUMINUM		CHK		D750351800				A01			
						FINISH:		ENG		D				SHEET 1 OF 1			
								MFG									
								QA									
TOLERANCES:		CORNERS EDGES BROKEN		OUTSIDE: 0.25 MAX		SCALE: 2:1											
3 PLACE 2 PLACE 1 PLACE ANGLES				INSIDE: 0.25 MAX													
±0.020 ±0.10 ±0.3 ±1°						WORKMANSHIP PER: N/A											