

8		7		6		5		4		3		2		1		
PART NUMBER												REV	CHG NO	DESCRIPTION		DATE
750352600																

F





E

D

C

B

A



F

E

D

C

B

A

EPDM		DIMENSIONS ARE IN MILLIMETER TOLERANCES: 3 PLACE 2 PLACE 1 PLACE ANGLES ±0.020 ±0.10 ±0.3 ±1°						6061-T6 ALUMINUM		CHK		OCP Acoustic Surrogate Top Cover		D750352600			A01			
STATE: TIME: DATE: VERSION:						CORNERS EDGES BROKEN		OUTSIDE: 0.25 MAX INSIDE: 0.25 MAX		FINISH:									ENG	
																			MFG	
																			QA	
																			WORKMANSHIP PER: N/A	