

		REVISIONS		
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	E1	RELEASE TO PROTOTYPE	7-20-10	B. Askarinam
	E2	OFFSET COUNTERSINK HOLES	9-6-10	P. Herman
	E3	CHANGED MAT'L, FINISH NOTE, ADDED TOLERANCE	10-20-10	P. Herman
	E4	UPDATE TOLERANCE FOR MFG.	7-19-12	B. Askarinam






NOTES: (UNLESS OTHERWISE SPECIFIED).


1. ALL DIMENSIONS IN INCHES.
2. INTERPRET DRAWING IN ACCORDANCE WITH ANSI Y14.5M.
3. THIS DRAWING SHOWS CRITICAL AND INSPECTION DIMENSIONS, TOLERANCING, AND NOTES. REFER TO CAD DATABASE FOR NOMINAL FABRICATION DATA.
4. ALL BEND RADII TO BE MINIMUM.
5. FINISH: NONE.
6. REMOVE ALL BURRS AND SHARP EDGES FOR SAFE HANDLING.
7. STAMP P/N# AND REV LEVEL WITH CONTRASTING INDELIBLE INK .12 HIGH CHARACTERS.


TOLERANCES:

ANGULAR..... ± 1°
XX..... ± .010
XXX..... ± .005

UNLESS OTHERWISE SPECIFIED







NOT TYPICAL

		NAME	APPROVED	DATE	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN	Bobby L		7-20-10	**INTERFACE MASTERS**
THIRD ANGLE PROJECTION	CHECKED				TITLE: N2948, MOLEX 8 PIN, HOT SWAP, BRACKET
INTERPRET PER ANSI Y14.5M-'94	ENGR	Bobby L			
PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INTERFACE MASTERS. ANY REPRODUCTION, IN PART OR AS A WHOLE, WITHOUT THE WRITTEN PERMISSION OF INTERFACE MASTERS CORP. IS PROHIBITED.	MATERIAL: GAL-XC				
	FINISH: SEE NOTE	SIZE D	DWG. NO. 001-IM3091	REV E4	
	FILE NAME: 001-IM3091.SLDDRW		SCALE: 1:1	SHEET 1 OF 1	