

		REVISIONS		
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	E1	RELEASE TO PROTOTYPE	11-8-10	P. HERMAN
	E2	CHANGED .575 DIM. TO .50 DIM	8-28-12	B. ASKARINAM
	E3	ADDED 4X MORE #6 COUNTERSINKS	10-28-12	B. ASKARINAM






NOTES: (UNLESS OTHERWISE SPECIFIED).


1. ALL DIMENSIONS IN INCHES.
2. INTERPRET DRAWING IN ACCORDANCE WITH ANSI Y14.5M.
3. THIS DRAWING SHOWS CRITICAL AND INSPECTION DIMENSIONS, TOLERANCING, AND NOTES. REFER TO CAD DATABASE FOR NOMINAL FABRICATION DATA.
4. ALL BEND RADII TO BE MINIMUM.
5. FINISH: POWDER COATED. RAVEN BLK W/ SATIN TEXTURE MT-1055. PAINT ENTIRE PART.
6. REMOVE ALL BURRS AND SHARP EDGES FOR SAFE HANDLING.
7. STAMP P/N# AND REV LEVEL WITH CONTRASTING INDELIBLE INK .12 HIGH CHARACTERS.

TOLERANCES:

ANGULAR..... ± 1°
XX..... ± .010
XXX..... ± .005

UNLESS OTHERWISE SPECIFIED





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		NAME	APPROVED	DATE
	DRAWN	Bobby L		11-8-10
THIRD ANGLE PROJECTION	CHECKED			
INTERPRET PER ANSI Y14.5M-'94	ENGR	Bobby L		

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INTERFACE MASTERS. ANY REPRODUCTION, IN PART OR AS A WHOLE, WITHOUT THE WRITTEN PERMISSION OF INTERFACE MASTERS CORP. IS PROHIBITED.

INTERFACE MASTERS

TITLE: N2818, N2948, N1314 LEFT MOUNTING EAR, IMT VERSION

MATERIAL: .074 GAL-XC

FINISH: SEE NOTE

SIZE: D | DWG. NO. 001-IM3131 | REV E3

FILE NAME: 001-IM3131.SLDDRW | SCALE: 1:1 | SHEET 1 OF 1