

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	E1	RELEASE TO PROTOTYPE	3-22-13	B. Askarinam





SECTION A-A
SCALE 3 : 1


NOTES: (UNLESS OTHERWISE SPECIFIED).


1. ALL DIMENSIONS IN INCHES.
2. INTERPRET DRAWING IN ACCORDANCE WITH ANSI Y14.5M.
3. THIS DRAWING SHOWS CRITICAL AND INSPECTION DIMENSIONS, TOLERANCING, AND NOTES. REFER TO CAD DATABASE FOR NOMINAL FABRICATION DATA.
4. ALL BEND RADII TO BE MINIMUM.
5. FINISH: POWDERCOATED. RAVEN BLK W/ SATIN TEXTURE MT-1055. PAINT ALL EXTERNAL SURFACES. ALLOW OVERSPRAY INSIDE.
6. REMOVE ALL BURRS AND SHARP EDGES FOR SAFE HANDLING.
7. STAMP P/N# AND REV LEVEL WITH CONTRASTING INDELIBLE INK .12 HIGH CHARACTERS.


TOLERANCES:

ANGULAR..... ± 1°
XX..... ± .010
XXX..... ± .005

UNLESS OTHERWISE SPECIFIED







		NAME	APPROVED	DATE
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN	Bobby L		3-22-13
THIRD ANGLE PROJECTION	CHECKED			
INTERPRET PER ANSI Y14.5M-'94	ENGR	Bobby L		

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INTERFACE MASTERS. ANY REPRODUCTION, IN PART OR AS A WHOLE, WITHOUT THE WRITTEN PERMISSION OF INTERFACE MASTERS CORP. IS PROHIBITED.

MATERIAL: .060 GAL-XC

FINISH: SEE NOTE

INTERFACE MASTERS

TITLE: FAN BRACKET, 40mm X 40mm X 56mm, HOT SWAP

SIZE: D | DWG. NO.: 001-IM3407 | REV: E1

FILE NAME: 001-IM3407.SLDDRW | SCALE: 1:1 | SHEET 1 OF 1