


SCALE 0.300

	PART NUMBER	Q'Y	DESCRIPTION
1	123100000869A	1	IRON BASE ES4630BH-0615-EC
2	124022-000	16	SCREW FHMS+BM
3	124600000070A	1	SPACER HFM 5 BRASS 10.7-M3-D ES4628BH-FLF-61
4	124025-010	13	SCREW PH MS NICKEL M3X6mm
5	114300000027A	1	MODULE BOARD R4.7AC AF8GSSGH-AC3 8G eUSB SSD
6	125500001600A	1	CABLE MOUNT

Reason		
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released,or disclosed without expressed written permission.	.	.
	.	.
	.	.
	.	.
	.	.
	ZONE	DESCRIPTION

UNSPECIFIED TOL'S (+/-0.2mm)

ANGLE +/- 1°	DIM \ GRADE	0	1	2	3	4	5
ROUGHNESS	0------16	0.05	0.1	0.15	0.2	0.2	0.5
	16------63	0.05	0.15	0.2	0.3	0.3	0.8
	63------250	0.05	0.2	0.25	0.4	0.5	1.2
	250------500	0.1	0.25	0.3	0.6	0.8	1.8
	500------1000		0.3	0.5	0.8	1.2	3.0

FINISH.

PART NO.

MATERIAL

SCALE 1/1	UNIT MM ~~(IN)~~
DESIGN Curtis	11-FEB-15

Accton TECHNOLOGY CORP.

DWG. TITLE.	SHEET 1/3	REV.	SIZE
PE_AS4610-30T		A0	A3