


ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
2	1	PANEL SIDE SM	433231	C32014
1	2	PROFILE STIFFENER SUPPORT SM	433232	C32015


BILL OF MATERIALS for PANEL SIDE WLD PART No. 433230







SCALE 0.5









DETAIL A
SCALE 1.0
4 POSNS




DETAIL E
SCALE 1.0
4 POSNS



DETAIL D
SCALE 0.5



DETAIL C
SCALE 0.5




NOTES

PLACE ALL FASTENERS INTO ***
(NOT SHOWN)

ITEM	QTY	DESCRIPTION	DRWG No.
3	2	SCREW, TAPTITE, PN HD, TORX, T30 M6x10x1.0p Z/P DIN 7500	429275_
2	1	LABEL, 2.5"x1"	413499_BULK
1	1	BAG 60x80mm GRIPSEAL 200g GL2 PRINTED	426241_BULK

BILL OF MATERIALS FOR FASTENER SIDE PANEL KIT ASM PART NO. C32014_KIT



SCALE 0.05

ITEM	QTY	DESCRIPTION	DRWG No.
3	0.25M	SELLOTAPE CLEAR 2"M/L REF: 425862	
2	1	PANEL SIDE PNT	C32014_PNT
1	1	FASTENER SIDE PANEL KIT ASM	C32014_KIT

BILL OF MATERIALS FOR PANEL SIDE ASM PART NO. C32014_ASM

NOTES

- FINISH:- PAINT BLACK
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
- DIMENSIONS CONTAINED IN AN OBROUND REQUIRE A CP OF 1.33
- MATERIALS SPECIFIC:- STEEL, MILD, COLD-ROLLED, to EN 10130:2006 Gr.DC01
- REFERENCE DRAWINGS: - No.
- REFER 3D CAD MODEL FOR WELD LOCATION DEFINITION
- RELEASE LEVEL: - Concept

Meta

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 9.1 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.10 @ A3

MATERIAL [.1] THK'

DESCRIPTION O.C.P. v3 O.C.P.

PANEL SIDE PNT

DWG No C32014_PNT

3

1 OF 1