NOTES

1. MATERIAL: MULTIPLE_MATERIALS
FINISH: RAL_9005

2. TOLERANCES ADDED TO DRAWING DIMENSIONS TAKE PRECEDENCE OVER OTHER TOLERANCES. DIMENSIONS MARKED CTF WILL BE MEASURED DURING CpK.


3. - UNFINISHED (SHEET METAL / RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS ACCORDING TO ISO 13715
- FINISHED COMPONENTS (PAINTED, PLATED, RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.

4. WELD SYMBOLS TO ISO 2553 UNLESS OTHERWISE STATED


5. ALL WELD LENGTH TOLERANCES +5/-0mm UNLESS OTHERWISE STATED ALL WELD HEIGHTS TO ISO 5817 UNLESS OTHERWISE STATED WELD LENGTH MEASUREMENTS TO BE TAKEN FROM START/FINISH OF COMPLETE WELD


6. REFERENCE DRAWINGS: Na

	CHANGE	ECN	DATE	NAME	ZONE
A	INITIAL CREATION	-	28/04/25	M.T	-
		-			-





SECTION B - B
SCALE 0.500






DETAIL C
SCALE 0.400





DETAIL B
SCALE 0.500



DETAIL D
SCALE 0.500

2	1	PROFILE FRONT RIGHT CABLE MANAGER SM	402843	C35736
1	1	BRACE FRONT RIGHT CABLE MANAGER SM	402844	C37109
ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
BILL OF MATERIALS FOR PROFILE FRONT RIGHT CABLE MANAGER WLD PART NO. 402842				

	1	PROFILE FRONT RIGHT CABLE MANAGER WLD	402842	C35734_WLD
	AS REQ.	PAINT: - RAL9005 2 PART DIP MIX	478517	478517
	AS REQUIRED 1	PAINT, RAL 9005, TEXT (CARBON BLACK)	406087	406087
ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
BILL OF MATERIALS FOR PROFILE FRONT RIGHT CABLE MANAGER PNT PART NO. 402841				

Meta

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 16.9 Kg

FOR UNSPECIFIED DIMENSIONS REFER TO 3D CAD. UNDIMENSIONED FEATURES TO BE INTERPRETED FROM 3D CAD FILE AND TOLERANCES FROM TOL. TABLE
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.08 @ A3

MATERIAL [.1] THK'

DESCRIPTION AQUATRON META

PROFILE FRONT RIGHT CABLE MANAGER WLD

DWG No C35734_WLD

B

1 OF 1