


OPEN
Compute Project

Optical Transceiver

800G OSFP112 2xSR4 (Air) to 2x400G OSFP112-RHS SR4 (immersion)

OCP Immersion Active Optical Cable (iAOC)

Specification V0.1

Product Specification
Effective July 15th, 2025

Author: Eric Chen, FormericaOE

Compliance with OCP Tenants

Openness

By migrating the Immersion Active Optical Cable & Pigtail Specifications to the Open Compute foundation, they become open to all to review and implement. In addition, the broad membership of the OCP is able to contribute to the future development of the specification.

Efficiency

The purpose of the Immersion Active Optical Cable Specification is to drive commonality in implementations of iAOCs/iAOPs in order to reduce friction in adoption users. This directly reduces opex in the form of qualifications and firmware work to adapt to different iAOC/iAOP implementations.

Impact

Immersion Active Optical Cables or Pigtails have proven to be essential components of hyperscale and service provider networks in order to enable high speed, low cost, low power and highly reliable networks. Migrating this specification to OCP drives commonality in these implementations and a broader membership base to widen impact.

Scale

Multiple hyperscalers have deployed or are planning to deploy Active Optical Cables. Soon they shall be deployed in immersion cooling.
Similarly to optical connectors in Air/DLC, the CMIS/DDMI monitoring functions ensure the Data Center Fabric is performing at its optimal.

Sustainability

Active Optical Cables & Pigtails ease fabric connection complexity. Immersion Active Optical Cables & Pigtails allows the fabric to function in immersion cooling, which lowers PUE of data centers for AI/ML/HPC.

Table of Contents

1 License 4
1.1 Scope 6
1.2 Overview 6
2 Common Terms 7
2.1 Parameter related 7
2.2 Product related 7
2.3 Fiber 8
2.4 Standard 8
3 Operating Conditions 9
4 Specifications 9
4.1 Electrical Transmitter Characteristic (Air side) 9
4.2 Electrical Receiver Characteristic (Air side) 10
4.3 Electrical Transmitter Characteristic (Immersion side) 10
4.4 Electrical Receiver Characteristic (Immersion side) 11
4.5 Optical Fiber Link Model 11
5 Form Factor 12
5.1 Mechanical Drawing 12
6 Management Interface 13
7 Immersion Cooling Requirements 14
8 Reference 14
9 Revisions 15

1 License

THE UPDATED DEFAULT CONTRIBUTOR LICENSE AGREEMENT (CLA) IS **OWFa 0.9**. PLEASE VERIFY THE CORRECT CLA/FSA IS USED AND EXECUTED FOR THIS CONTRIBUTION.

1.1. Open Web Foundation (OWF) CLA

Contributions to this Specification are made under the terms and conditions set forth in **Modified Open Web Foundation Agreement 0.9 (OWFa 0.9)**. (As of October 16, 2024) ("Contribution License") by:

Formerica Optoelectronics Inc

Usage of this Specification is governed by the terms and conditions set forth in **Modified OWFa 0.9 Final Specification Agreement (FSA)** (As of October 16, 2024) **("Specification License").**

You can review the applicable Specification License(s) referenced above by the contributors to this Specification on the OCP website at https://www.opencompute.org/contributions/templates-agreements.

For actual executed copies of either agreement, please contact OCP directly.

Notes:

The above license does not apply to the Appendix or Appendices. The information in the Appendix or Appendices is for reference only and non-normative in nature.

NOTWITHSTANDING THE FOREGOING LICENSES, THIS SPECIFICATION IS PROVIDED BY OCP "AS IS" AND OCP EXPRESSLY DISCLAIMS ANY WARRANTIES (EXPRESS, IMPLIED, OR OTHERWISE), INCLUDING IMPLIED WARRANTIES OF MERCHANTABILITY, NON-INFRINGEMENT, FITNESS FOR A PARTICULAR PURPOSE, OR TITLE, RELATED TO THE SPECIFICATION. NOTICE IS HEREBY GIVEN, THAT OTHER RIGHTS NOT GRANTED AS SET FORTH ABOVE, INCLUDING WITHOUT LIMITATION, RIGHTS OF THIRD PARTIES WHO DID NOT EXECUTE THE ABOVE LICENSES, MAY BE IMPLICATED BY THE IMPLEMENTATION OF OR COMPLIANCE WITH THIS SPECIFICATION. OCP IS NOT RESPONSIBLE FOR IDENTIFYING RIGHTS FOR WHICH A LICENSE MAY BE REQUIRED IN ORDER TO IMPLEMENT THIS SPECIFICATION. THE ENTIRE RISK AS TO IMPLEMENTING OR OTHERWISE USING THE SPECIFICATION IS ASSUMED BY YOU. IN NO EVENT WILL OCP BE LIABLE TO YOU FOR ANY MONETARY DAMAGES WITH RESPECT TO ANY CLAIMS RELATED TO, OR ARISING OUT OF YOUR USE OF THIS SPECIFICATION, INCLUDING BUT NOT LIMITED TO ANY LIABILITY FOR LOST PROFITS OR ANY CONSEQUENTIAL,

INCIDENTAL, INDIRECT, SPECIAL OR PUNITIVE DAMAGES OF ANY CHARACTER FROM ANY CAUSES OF ACTION OF ANY KIND WITH RESPECT TO THIS SPECIFICATION, WHETHER BASED ON BREACH OF CONTRACT, TORT (INCLUDING NEGLIGENCE), OR OTHERWISE, AND EVEN IF OCP HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Scope and Overview

1.1 Scope

This document defines the technical specifications for the 800G OSFP112 2xSR4 (Air) to 2x400G OSFP112-RHS SR4 (Immersion) OCP Immersion Active Optical Cable (iAOC) used in large-scale data center applications.

1.2 Overview

The 800G OSFP112 2xSR4 (Air) to 2x400G OSFP112-RHS SR4 (Immersion) iAOC OCP optical specification is based on 2x400GBASE-SR4 as defined in IEEE 802.3 ck and IEEE 802.3 bs.

This optimization involves the adoption of coolant-compatible materials, preservation of optical path integrity, and validated thermal performance to ensure reliable operation in immersion liquid-cooling environments. Considering the characteristics of liquid cooling fluid and the operation mode of the cooling system, temperature specifications of the product have been relaxed. The temperature range shall be relaxed from 0-70°C to RT-70°C. (Note, the RT value depends on dew point of the air).

While this specification is focused on 2x400G operation, the module shall be compliant to the IEEE 802.3 ck and IEEE 802.3 bs.

2 Common Terms

The following terms are used in this document

2.1 Parameter related

AOP - Average Optical Power
OMA - Optical Modulation Amplitude
TDECQ - Transmitter Dispersion Eye Closure Quaternary
ER - Extinction Ratio
SMSR - Side Mode Suppression Ratio
BER - Bit Error Rate
FEC - Forward Error Correction
PAM4 - 4-level Pulse Amplitude Modulation
Gbps - Gigabit per second
GBd - Gigabaud

2.2 Product related

iAOP - Immersion Active Optical Pigtail
iAOC - Immersion Active Optical Cable
AOC - Active Optical Cable
CT - Commercial Temperature
IT - Industrial Temperature
LPMode - Low Power Mode
I2C - Inter-Integrated Circuit
SR - Short reach
LR - Long reach

2.3 Fiber

MMF - Multi-Mode Fiber
SMF - Single-Mode Fiber
OM3 - Optical Multimode 3
PC - Physical Contact
APC - Angled Physical Contact
MPO - Multiple-Fiber Push-On

2.4 Standard

CWDM - Coarse Wavelength Division Multiplex
IEEE - Institute for Electrical and Electronics Engineers
MSA - Multi-Source Agreement
SFF - Small Form Factor
QSFP - Quad Small Form Factor Pluggable
QSFP112 - Quad Small Form Factor Pluggable Module 112
QSFP-DD - QSFP–Double Density
OSFP - Octal Small Form Factor Pluggable Module
OSFP-RHS - OSFP-Riding Heat Sink
CMIS - Common Management Interface Specification

3 Operating Conditions

Recommended Operating Conditions		
Parameters	**Value**	**Unit**
Case Operating Temperature	Air = 0 ~ 70	℃
	Immersion = RT ~ 70 **Note1**	
Power Supply Voltage (Typical)	3.3	V
Power Consumption (Max)	Air = 15	W
	Immersion = 10	
Data Rate per Channel (Typical)	53.125	GBd

Note1: RT (Room Temp) value depends on dew point of the air

4 Specifications

4.1 Electrical Transmitter Characteristic (Air side)

Parameter	**Value**	**Unit**
Signaling Rate, each lane	53.125 ± 100 ppm	GBd
Differential Input Voltage Tolerance(min)	750	mV
Effective Return Loss(min)	8.5	dB
Single-ended Input Voltage	-0.4~3.3	V
DC Common-mode Input Voltage	-0.35~2.85	V
Differential Termination Mismatch(max)	10	%
AC Common-mode Voltage Tolerance Low-frequency, VCMLF Full-band, VCMLF	 32 80	mV
Differential to Common-mode Return loss, RLcd	IEEE 802.3 ck D3.3 Equation 120G-2	dB

4.2 Electrical Receiver Characteristic (Air side)

Parameter	Value	Unit
Signaling Rate, each lane	53.125 ± 100 ppm	GBd
Peak-to-Peak AC Common Mode Voltage Low-frequency, VCMLF Full-band, VCMLF	32 80	mV
Differential Peak-to-Peak Output Voltage Short Mode Long Mode	600 845	mV
Eye Height(min)	15	mV
Vertical Eye Closure(max)	12	dB
Effective Return Loss(min)	8.5	dB
DC Common-mode Voltage Tolerance	-0.35~2.85	V
Transition Time(min)	8.5	ps
Differential Termination Mismatch(max)	10	%
Common-mode to differential return loss, RLdc	IEEE 802.3ck Equation 120G-1	dB

4.3 Electrical Transmitter Characteristic (Immersion side)

Parameter	Value	Unit
Differential Input Voltage Tolerance (TP1a)(min)	750	mV
Single-ended Voltage Tolerance Range(min)	-0.4~3.3	V
DC Common-mode Voltage Tolerance(min)	-0.35~2.85	V
Differential Termination Mismatch(max)	10	%

4.4 Electrical Receiver Characteristic (Immersion side)

Parameter	Value	Unit
AC Common-mode output Voltage (RMS)(max)	25	mV
Differential Output Voltage Short Mode / Long Mode(max)	600 / 845	mV
Near-end Eye height, differential(min)	70	mV
Far-end Eye height, differential(min)	30	mV
Far-end pre-cursor ratio	-4.5~2.5	%
DC Common-mode Voltage Tolerance	-0.35~2.85	V
Transition Time (min, 20% to 80%)(min)	9.5	ps
Differential Termination Mismatch(max)	10	%

4.5 Optical Fiber Link Model

The reference optical fiber link model is based on MMF fiber. The distance. Refer to IEEE 802.3 ck and IEEE 802.3 bs.

Optical Fiber Link Model	
2x400GBase-SR4	2m to 50m for OM3


5 Form Factor

The OSFP112 and OSFP112-RHS form factor described in OSFP MSA shall be used. This form factor is commonly referred to as OSFP MSA for 800G to 2x400G applications.

5.1 Mechanical Drawing


2x400G OSFP112-RHS SR4 Flat Top (Immersion)

800G OSFP112 2xSR4 Finned Top/Type 2 (Air)



6 Management Interface

The module is compliant to CMIS.



7 Immersion Cooling Requirements

Immersion products must be materially compatible with the immersion fluid and perform equal or better in the immersion fluid.

This involves utilizing the testing conditions specified in the OCP “Material Compatibility in Immersion Cooling” guideline (80°C, 0.8L, 336 hours) and adhering to the acceptance criteria to determine if the material is compatible (< 10% change in weight, length, diameter, etc. before and after test).

Only compatible materials should be used in immersion products.

8 Reference

The following documents are referenced in this specification:

IEEE 802.3 ck, IEEE 802.3 bs
CMIS
OSFP MSA
QSFP112 MSA
OCP Material Compatibility in Immersion Cooling Rev 1.0
OCP Immersion Requirements Rev 2.1

9 Revisions

Rev	Date	Description
0.1	July 15th, 2025	Initial Release