




NOTES

- FINISH:- PAINT BLACK
- MATERIALS SPECIFIC:-STEEL, MILD, COLD-ROLLED, to EN 10130:2006 Gr.DC01
- DIMENSIONS & TOLERANCES INDICATED INCLUDE PAINT
- PAINT THICKNESS APPLIED = 0.12±10%
- ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- GEOMETRY:- L/H AND RIGHT COMPONENTS REQUIRED (L/H FULLY DIMENSIONED)
- RELEASE LEVEL: - ECN Production

1+0.12

PROVISIONAL ONLY
FOR EVALUATION / TRIALS / REVIEW
NOT FOR PRODUCTION MANUFACTURE

REV.	CHANGE	E.C.N.	DATE	NAME	CHK	ZONE
2	FASTENER CLEARANCE	9590	18/AUG/22	P.C.		
1	N.P.I. RELEASE	9571	20/JUN/22	D.P.W		

THIRD ANGLE PROJECTION.

MASS APPROX.

3.4 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:

0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.15 @ A3

MATERIAL MILD-STEEL-DC01 1.2 THK'


DESCRIPTION O.C.P. V3 META

PROFIE CABLE MNG' L/H SM


DWG No C29054_LH

2

1 OF 2



DETAIL A
SCALE 0.700



20x POSITIONS
BRIDGE FORM DETAIL H
SCALE 1.0

SCALE	0.15 @ A3	
MATERIAL	MILD_STEEL_DC01	
DESCRIPTION	O.C.P. V3	META
PROFILE CABLE MNG' L/H SM		
DWG No	C29054_LH	ISS.
		3
DRAWING SHEET 2 OF 2		