






T.S.F. PLNGR GRN(SOUTHCO 56-171-2-059)




2	1	T.S.F. PLNGR GRN(SOUTHCo 56-171-2-059)	432444	56-171-2-059
1	1	BRACKET RETAINING LEVELLING FOOT PNT	432574	C29997_PNT
ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
BILL OF MATERIALS FOR C29997 PLATE RETAINING LEVELLING FOOT ASM PART NO 432573				

NOTES

- FINISH:- PAINT BLACK
- PAINT THICKNESS APPLIED = 0.12MM±10%
- DIMENSIONS AND TOLERANCES AFTER PAINT, UNLESS SPECIFIED OTHERWISE
- MATERIALS SPECIFIC: - STEEL, STRUCTURAL, HOT-ROLLED, to EN 10149-2 Gr.S355MC
- REFERENCE DRAWINGS: - Na.
- SHARP EDGES & BURRS: - UNFINISHED (SHEET METAL / RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS ACCORDING TO ISO 13715
- FINISHED COMPONENTS (PAINTED, PLATED, RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- PLUNGER HOLE DIAMETER WITHOUT PAINT AND WITH PAINT MENTIONED
- RELEASE LEVEL: - ECN Production



1	ECN 9571	17/06/22	P.C	R.B
ISS.	E.C.N. No / DESCIP	DATE	NAME	CHK'D

		SCALE 1:00 @ A3	
		MATERIAL STEEL S355MC HR BSEN10149-2 3.0 THK	
THIRD ANGLE PROJECTION.	MASS APPROX.	0.04 Kg	DESCRIPTION v3 META
	TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD: 0.0 : ±0.8 0.00 : ±0.5 0.000 : ±0.25 ANGLES : ±1.0°		
 ALL DIM'S ARE IN MM.		BRACKET RETAINING LEVELLING FOOT PNT	
		DWG No C29997	1 OF 1
CRITICAL DIMENSION			