




NOTE:

PART IS HANDED,C30720_1 AS DETAILED, C30720_2 OPPOSITE HAND

ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715.

FINISH, PAINT BLACK

DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%



SCALE 1.00 @ A3	
MATERIAL STEEL_S355MC_HR_BSEN10149-2 3.0 THK	
DESCRIPTION	META
BRACE MEMB JOGGLE PLATE 1 SM	
DWG No	1
C30720_1 / C30720_2	1 OF 1

THIRD ANGLE PROJECTION.	MASS APPROX.	0.0 Kg
		TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
		0.0 : ±0.8
		0.00 : ±0.5
		0.000 : ±0.25
		ANGLES : ±1.0°
		(CRITICAL DIMENSION)

1	ECN 9571	11/06/22	DPW	
ISS.	E.C.N. No / DESCRIP	DATE	NAME	CHK'D

