




NOTES

- GEOMETRY:- L/H AND R/H COMPONENTS REQUIRED (L/H FULLY DIMENSIONED)

- FINISH:- PAINT BLACK

- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%

- ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.)

1

ECN 9571

20/06/22

DPW

ISS.

E.C.N. No / DESCRIP.

DATE

NAME

CHK'D

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX.

0.2 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:

0.0 ± 0.8

0.00 ± 0.5

0.000 ± 0.25

ANGLES ± 1.0°

CRITICAL DIMENSION

SCA 0.50 @ A3

MATERIAL

MILD_STEEL_DC01 1.2 THK'

DESCRIPTION

OCP V3

META

COVER CLAMP STRIP RACK GSK- UP LH PNT

COVER CLAMP STRIP RACK GSK - UP RH PNT

DWG No

C31243_LH

C31243_RH

2

1 OF 1