




NOTES

- GEOMETRY: LH AND RH COMPONENTS REQUIRED (LH SHOWN DIMENSIONED)
- FINISH:- PAINT BLACK
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12± 10%
- UNFINISHED (SHEET METAL / RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS ACCORDING TO ISO 13715
- FINISHED COMPONENTS (PAINTED, PLATED, RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- RELEASE LEVEL: - ECN Production

2

ECN 9590

04/04/23

DPW

ISS.

E.C.N. No / DESCRIP.

DATE

NAME

CHK'D

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX.

0.05 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:

0.0 ± 0.8

0.00 ± 0.5

0.000 ± 0.25

ANGLES ± 1.0°

CRITICAL DIMENSION

SCA1100

@ A3

MATERIAL

MILD_STEEL_DC01 1.2 THK'

DESCRIPTION

v3

META

COVER CLAMP STRIP RACK GSK LWR KIT L/H SM

DWG No

C31388_LH

C31388_RH

2

1 OF 1