




NOTES

- GEOMETRY:- L/H AND R/H COMPONENTS REQUIRED(R/H FULLY DIMENSIONED)
- FINISH:- PAINT BLACK
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
- ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.)

1	ECN 9571	20/06/22	DPW	
ISS.	E.C.N. No / DESCRIP.	DATE	NAME	CHK'D



THIRD ANGLE PROJECTION.	MASS APPROX.	0.2 Kg
TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD: 0.0 ± 0.8 0.00 ± 0.5 0.000 ± 0.25 ANGLES ± 1.0°		
CRITICAL DIMENSION		

SCA 0.50 @ A3		
MATERIAL	MILD_STEEL_DC01 1.2 THK'	
DESCRIPTION	OCP V3	META
COVER CLAMP STRIP RACK GSK - MID LH PNT COVER CLAMP STRIP RACK GSK - MID RH PNT		
DWG No	C31639_LH C31639_RH	2
		1 OF 1