







NOTES


- GEOMETRY: L/H AND R/H COMPONENTS REQUIRED (L/H FULLY DIMENSIONED)
- FINISH: BLACK
- MATERIAL/FLAMMABILITY RATING : POLYMER_PC_ABS, RATED TO U.L. 94 V0
NON CHLORINATED, NON BROMINATED.
- SPECIFIC GRADE : JH960-6950-C2B-S0759
CONTAINS 50% POST CONSUMER MATERIAL
- ALL DRAFT ANGLES : 1°
- REFERENCE DRAWINGS: REFER TO 3D MODEL
- RELEASE LEVEL: - Production

1	ECN9571	17/06/22	DPW		
ISS.	E.C.N. No / DESCIP	DATE	NAME	CHK'D	


Meta			SCALE 1.00 @ A3		
THIRD ANGLE PROJECTION.  ALL DIM'S ARE IN MM.			MATERIAL POLYMER_PC_ABS		
			DESCRIPTION V3 OPEN RACK META		
			BUSHING GROMMET CANOPY L/H		
			BUSHING GROMMET CANOPY R/H		
MASS APPROX. 0.02 Kg			DWG No C31988_LH		1
TOLERANCE UNLESS OTHERWISE STATED: ANSI STANDARD: 0.0 : ±0.8 0.00 : ±0.5 0.000 : ±0.25 ANGLES : ±1.0°			C31988_RH		
CRITICAL DIMENSION					1 OF 2




SECTION E - E
SCALE 2.000




SECTION C - C
SCALE 2.000



SECTION D - D
SCALE 2.000



DETAIL A
SCALE 3.000



DETAIL B
SCALE 3.000

SCALE	1.00 @ A3	
MATERIAL	POLYMER_PC_ABS	
DESCRIPTION	V3 OPEN RACK	META
BUSHING GROMMET CANOPY L/H		
BUSHING GROMMET CANOPY L/H		
DWG No	C31988_LH	ISS.
	C31988_LH	1
DRAWING SHEET 2 OF 2		