


PROVISIONAL ONLY
FOR EVALUATION / TRIALS / REVIEW
NOT FOR PRODUCTION MANUFACTURE

DIMENSIONS CONTAINED IN AN OBROUND REQUIRE A CP OF 1.33

±0.20

ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
2	1	SHELF POWER LH 10U SM	433579	C33178_LH
1	1	LEVER SHELF RELEASE SPRING CLIP v2 SM	433164	C32615

BILL OF MATERIALS

NOTES

- ALL GEOMETRICAL TOLERANCES CONSIDERED "CRITICAL" CP= 1.33. BASIC DIMENSIONS ARE CONTAINED IN A RECTANGULAR BOX WITH THE TOLERANCE RANGE DEFINED IN THE ASSOCIATED GEOMETRICAL TOLERANCE.
- GEOMETRY:- L/H AND RIGHT COMPONENTS REQUIRED (R/H FULLY DIMENSIONED)
- FINISH:- Z/P 38µ TARGET THK'NES
- FINISHED COMPONENTS (PAINTED, PLATED, RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
 ° HIGHLIGHTED EDGES REQUIRE SECONDARY DE-BURRING OPERATION, BUILT INTO HARD-TOOL, OR MANUAL POST PIERCE DE-BURRING OPERATION.
- MATERIALS (SPECIFIC): -STEEL, METALLIC COATED DX51D, Z/P 275g/m² (19µ LAYER) to EN 10346. QUALITY A.
 YOUNGS MODULUS: 200GPa±20GPa
 POISSONS RATIO: 0.27-0.3
 MIN.YIELD STRENGTH : 140MPa
- RELEASE LEVEL: - ECN Production

REV.	CHANGE	REVISION TRACKING	ECN	DATE	NAME	CHK	ZONE
1	N.P.I. (+ txt 'Ver A')	VERSION "A" I.D.MARK	E.C.N.9826	21/NOV/23	P.C.	TBC	MULTI

Meta

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 0.7 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.25 @ A3

MATERIAL
STEEL_METALLIC_COATED_DX51D_275 2.0 THK'

DESCRIPTION
O.C.P. V3 | FACEBOOK

SHELF POWER LH 10U SM
SHELF POWER RH 10U SM

DWG No
C33178_LH
C33178_RH

1

1 OF 1