




NOTES

- FINISH:- PAINT BLACK
- APPLIES TO BOM ITEM #1 (NO PIANT ALLOWED ON THE THREAD ON STUD)
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
- REFERENCE DRAWINGS: - Na
- RELEASE LEVEL: - Concept

2	2	T.S.F. SELF CLINCH STUD PEM FH-M8-25-Z1	432457	FH-M8-25-Z1
1	1	BRACKET CLAMP LOWER MANIFOLD PNT	0	C31186_PNT
ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
BILL OF MATERIALS for BRACKET CLAMP LOWER MANIFOLD ASM PART NO: 0				

REV.	CHANGE	DATE	NAME	CHK	ZONE
C	HOLE TOL + DIMS TO PLATE	10MAY/24	P.C.		
B	UPDATE	09/06/21	DPW		

		SCALE 2.00 @ A3	
		MATERIAL MILD-STEEL-DC01 3.0 THK'	
THIRD ANGLE PROJECTION.		MASS APPROX. 0.1 Kg	DESCRIPTION OCP V3 META
		TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:	BRACKET CLAMP LOWER MANIFOLD ASM
		0.0 : ±0.8 0.00 : ±0.5 0.000 : ±0.25 ANGLES : ±1.0°	
ALL DIM'S ARE IN MM.		CRITICAL DIMENSION	DWG No C31186
			C 1 OF 1