




NOTES

- FINISH: - PAINT BLACK
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
- REFERENCE DRAWINGS: - No.
- REFER TO 3D CAD MODEL FOR WELD LOCATION DEFINITION
- CONFORM TO UL 1439.
- PART IS HANDED C31654_LH_PAINT SHOWN DETAILED C31654_RH_ASM OPPOSITE HAND
- MATERIALS SPECIFIC: - STEEL, MILD, COLD-ROLLED, to EN 10130:2006 Gr.DC01
- RELEASE LEVEL: - Concept

REV.

CHANGE

E.C.N.

DATE

NAME

CHK

ZONE

C

UPDATED

No

26/MAR/24

P.C.

S.A.

C6

B

UPDATED

No

08/JUN/22

P.C.

D.W.

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

Meta

SCALE 1.00 @ A3

MATERIAL MILD_STEEL_DC01 3.0 THK'

DESCRIPTION v3 META

BRACKET COOL. UPPER L/H SM

DWG No C31654_LH_PAINT C31654_RH_PNT

C

1 OF 1

MASS APPROX. 0.3 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION