











SCALE= 0.250






NOTES

- NOTES
1. QC. DIM BE SPECIFIED AS (1)~(3)
 2. ALL PARTS ARE ROHS COMPLIANT
 3. TEXTURED SURFACES ON OUTSIDE: MT11010

Reason			UNSPECIFIED TOL'S (± 0.2 mm)										 FINISH. COLOR=EC16051 WHITE					
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.			ANGLE ±1°	DIM.	GRADE	0	1	2	3	4	5	PART NO. 123200000865A MATERIAL PC945NC, UL=94, V0 VERDER:8B1C	SCALE 1 / 2 UNIT MM <u>LIN</u>					
			ROUGHNESS			0	16	0.05	0.1	0.15	0.2		0.2	0.8	DESIGN Yvonne 06/21/19			
						16	63	0.05	0.15	0.2	0.3		0.3	0.8				
						63	250	0.05	0.2	0.25	0.4		0.5	1.2				
						250	500	0.1	0.25	0.3	0.6		0.8	1.8				
						500	1000	0.3	0.5	0.8	1.2	3.0						
ZONE	DESCRIPTION												DWG. TITLE		SHEET 1 / 1		REV.	SIZE
													COVER AP1024A-V2-1215-ZZ				A0	A3




SCALE= 1.000



NOTES
1. QC, DIM BE SPECIFIED AS (1)~(2)
2. ALL PARTS ARE ROHS COMPLIANT
3.TEXTURED SURFACES ON TOPSIDE: MT11020

Reason			UNSPECIFIED TOL'S (± 0.2 mm)								 FINISH		Accton TECHNOLOGY CORP.					
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.			ANGLE ±1 °	DIM.	GRADE	0	1	2	3	4	5	NO COATING						
			ROUGHNESS	0	16	0.05	0.1	0.15	0.2	0.2	0.3	PART NO.		SCALE 2 / 1 UNIT <u>MM</u>				
				16	63	0.05	0.15	0.2	0.3	0.3	0.8	DESIGN Yvonne 06/21'19						
				63	250	0.05	0.2	0.25	0.4	0.5	1.2							
				250	500	0.1	0.25	0.3	0.6	0.8	1.8							
				500	1000		0.3	0.5	0.8	1.2	3.0	MATERIAL PC141R, UL=94, HB VERDER:SABIC		DWG. TITLE		SHEET 1 / 1	REV.	SIZE A3
	ZONE	DESCRIPTION											LIGHTPIPE AP1024A-V2-1215-ZZ					



Reason			UNSPECIFIED TOL'S (± 0.2 mm)										 FINISH.							
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.			ANGLE	DIM.	GRADE	0	1	2	3	4	5	PART NO.	SCALE 2 / 1						UNIT	MM
			± 1 °			0	0.05	0.1	0.15	0.2	0.2		0.3	DESIGN	Yvonne	06/21/19	DWG. TITLE	SHEET 1 / 1	REV.	SIZE
			ROUGHNESS	16	63	0.05	0.15	0.2	0.3	0.3	0.8									
				63	250	0.05	0.2	0.25	0.4	0.5	1.2									
				250	500	0.1	0.25	0.3	0.6	0.8	1.8									
				500	1000	0.3	0.5	0.8	1.2	3.8										
			MATERIAL																	
ZONE		DESCRIPTION											ASSEMBLE AP1024A-V2-1215-ZZ				A3			