

This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.





Accton Inc.
Making Partnership Work

Model Name		ES6632BT2-1014-JN		Rev	R01
Size	A	Page Name	Block diagram	Engineer	Eason_Liu
Date:	Thursday, April 30, 2015			Sheet	1 of 3




Slave address will be 0x70 (default), 0x72, 0x74, 0x76
For non-redundant power supply, the slave address for I2C function should be 0x70.

System addressing	0/0	0/1	1/0	1/1
Address1 (A1) /Address0 (A0)				
Power supply I2C slave address	70h	72h	74h	76h



Pin Name	Description
PS On	0 : 12V output 1 : 12V not output
PS 12V OK	1 : 12V output Good 0 : 12V output fail
PS ALERT	1 : OK 0 : Alert to system
PS Present	0 : Present 1 : Not present

Golden Finger



This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.



Accton Inc.
Making Partnership Work

Model Name		ES6632BT2-1014-JN	Rev	R01
Size	Page Name	POWER_BOARD	Engineer	Eason_Liu
C				
Date:		Thursday, April 30, 2015	Sheet	2 of 3