






TOP SIDE HIGH LIMITED=10mm



Reason	.	.	UNSPECIFIED TOL 'S (+/- 0.2mm)										 FINISH.																		
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.	.	.	ANGLE +/- 1°	DIM	GRADE										PART NO.																
	.	.			0	1	2	3	4	5																					
	.	.			0.05	0.1	0.15	0.2	0.2	0.3																					
	.	.			0.05	0.15	0.2	0.3	0.3	0.8																					
	.	.			0.05	0.2	0.25	0.4	0.5	1.2																					
.	.	.	ROUGHNESS	DIM	16	63	250	500	500	500					SCALE 1/1	UNIT MM [IN]															
.	.	0.05			0.15	0.2	0.3	0.3	0.8																						
.	.	0.05			0.2	0.25	0.4	0.5	1.2																						
.	.	0.1	0.25		0.3	0.6	0.8	1.8																							
.	.	0.3	0.5		0.8	1.2	3.0																								
ZONE	DESCRIPTION												MATERIAL																		
													PCB T=3.0mm +/- 10%																		
													Accton TECHNOLOGY CORP.																		
													DWG. TITLE. SHEET 1/1 REV. SIZE																		
													PSU-BOARD-18J-SIAD2-TOP A6 A3																		