






ITEM	PART NUMBER	DESCRIPTION	Q'ty
1		Adapter Tray	1
2		Adapter Latch	2
3	Pingood MHL-23	Adapter Latch Handle	2
4		Adapter C Handle	2
5		Adapter Spring	2
6	JIU-YAN Z-T018B	Adapter Tape	2

Reason				UNSPECIFIED TOL 'S (±0.2 mm)										 FINISH.						
This document and the technical data disclosed are proprietary to Acclon Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.				ANGLE ± 1°	GRADE		0	1	2	3	4	5		PART NO. 123400000906A	SCALE 0.2/1		UNIT	MM [IN]		
							0	16	0.05	0.1	0.15	0.2			0.2	0.5	DESIGN	BRENT	02-JUL-14	
								16	63	0.05	0.15	0.2			0.3	0.3				0.8
								63	250	0.05	0.2	0.25			0.4	0.5				1.2
								250	500	0.1	0.25	0.3			0.6	0.8				1.8
								500	1000	0.3	0.5	0.8			1.2	3.0				
ZONE		DESCRIPTION													MATERIAL SGCC T=1.6mm					


Accton TECHNOLOGY CORP.

DWG. TITLE ADAPTER-TRAY-ORSA-1U




SHEET 0/4

REV. A1

SIZE A3






Reason			UNSPECIFIED TOL 'S (±0.2 mm)												FINISH.					
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.		ANGLE ±1°	DIM.	GRADE	0	1	2	3	4	5	PART NO. 123400000906A	SCALE 0.2 / 1		UNIT	MM [IN]					
		ROUGHNESS	0	16	0.05	0.1	0.15	0.2	0.2	0.5		DESIGN	BRENT	02-JUL-14						
			16	63	0.05	0.15	0.2	0.3	0.3	0.8										
			63	250	0.05	0.2	0.25	0.4	0.5	1.2										
			250	500	0.1	0.25	0.3	0.6	0.8	1.8										
ZONE	DESCRIPTION		500	1000	0.3	0.5	0.8	1.2	3.0	MATERIAL SGCC T=1.6mm					DWG. TITLE		SHEET 1 / 4		REV. A1	SIZE A3
																ADAPTER-TRAY-ORSA-IU				






Reason		UNSPECIFIED TOL 'S (±0.2 mm)										FINISH.										
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.	ZONE	DESCRIPTION	ANGLE ± 1°	ROUGHNESS	DIM. GRADE									PART NO. 123400000906A			SCALE 1 / 1		UNIT MM [IN]			
					0	16	0.05	0.1	0.15	0.2	0.2	0.5										
					16	63	0.05	0.15	0.2	0.3	0.3	0.8										
					63	250	0.05	0.2	0.25	0.4	0.5	1.2										
					250	500	0.1	0.25	0.3	0.6	0.8	1.8										
					500	1000	0.3	0.5	0.8	1.2	3.0	MATERIAL SUS301 T=0.8mm			DWG. TITLE ADAPTER-TRAY-ORSA-IU		SHEET 2 / 4		REV. A1		SIZE A3	


Accton TECHNOLOGY CORP.



Reason			UNSPECIFIED TOL 'S (±0.2 mm)										 FINISH. _____			Accton TECHNOLOGY CORP.								
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.			ANGLE ± 1°	DIM.	GRADE	0	1	2	3	4	5	PART NO. 123400000906A		SCALE 0.4/1	UNIT MM [IN]									
			ROUGHNESS	16	63	0.05	0.15	0.2	0.3	0.3	0.8	DESIGN BRENT		02-JUL-14										
				63	250	0.05	0.2	0.25	0.4	0.5	1.2													
				250	500	0.1	0.25	0.3	0.6	0.8	1.8													
				500	1000		0.3	0.5	0.8	1.2	3.0													
ZONE	DESCRIPTION													MATERIAL JIU-YAN Z-T018B			DWG. TITLE ADAPTER-TRAY-ORSA-1U				SHEET 3 / 4		REV. A1	SIZE A3



SCALE 2.000



Reason				UNSPECIFIED TOL 'S (±0.2 mm)												FINISH.		Accton TECHNOLOGY CORP.								
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released, or disclosed without expressed written permission.		ANGLE ± 1°	ROUGHNESS	DIM.	GRADE							PART NO.		SCALE 0.2/1		UNIT MM [IN]										
				0	16	0.05	0.1	0.15	0.2	0.2	0.5	123400000906A														
				16	63	0.05	0.15	0.2	0.3	0.3	0.8	DESIGN BRENT		02-JUL-14												
				63	250	0.05	0.2	0.25	0.4	0.5	1.2	MATERIAL SUS301 T=0.3mm														
				250	500	0.1	0.25	0.3	0.6	0.8	1.8															
ZONE		DESCRIPTION			500	1000	0.3	0.5	0.8	1.2	3.0							DWG. TITLE		SHEET 4 / 4		REV. A1		SIZE A3		
																					ADAPTER-TRAY-ORSA-1U					