




SECTION A-A





SCALE 1.000





DETAIL A
SCALE 4.000





SCALE 1.000

NOTES:
1. ALL DIMENSIONS SHOWN IN MILLIMETERS.
2. DIMENSIONS (1)~(3) ARE IQC CHECKPOINT.
3. ALL DIMENSIONS MUST BE MEASURED FOR FIRST ARITICAL APPROVAL.
4. ALL CRITICAL DIMENSIONS SHOWN MUST MEET A MINIMUM CPK VALUE OF 1.33.
5. ALL NON-SHOWN DIMENSION IN THE DRAWING, MUST BE TAKEN FROM 3D DATA.
6. THE DIMENSIONS NEED TO FOLLOW STANDARD DRAWING TOLERANCES TABLE AS BELOW UNLESS OTHERWISE STATED.
7. ALL PARTS MUST BE RoHS COMPLIANT.
8. ALL PARTS TO ABIDE TO FB COSMETIC AND INSPECTION GUIDELINES.

Reason			
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released,or disclosed without expressed written permission.	12	MODIFY THE NOTES.	
	,	,	
	,	,	
	,	,	
	,	,	
	ZONE	DESCRIPTION	

UNSPECIFIED TOL'S (+/-0.2mm)

ANGLE +/- 1°	DIM \ GRADE	0	1	2	3	4	5
ROUGHNESS	0------16	0.05	0.1	0.15	0.2	0.2	0.5
	16------63	0.05	0.15	0.2	0.3	0.3	0.8
	63------250	0.05	0.2	0.25	0.4	0.5	1.2
	250------500	0.1	0.25	0.3	0.6	0.8	1.8
	500------1000		0.3	0.5	0.8	1.2	3.0

FINISH.
COLOR: PANTONE 375C GREEN

PART NO. 123400001141A
SCALE 1/1 UNIT MM ~~IN~~
DESIGN Curtis 29-MAY-16
MATERIAL SABIC PC 945A UL94-V0

facebook

DWG. TITLE. LUGGAGE TAB BRACKET ES7632BT-0415-168FB
SHEET 1/1
REV. 02
SIZE A3