






SCALE 0.500








SCALE 0.500





SCALE 0.500

NOTES:
1. ALL DIMENSIONS SHOWN IN MILLIMETERS.
2. DIMENSIONS (1)~(3) ARE IQC CHECKPOINT.
3. ALL DIMENSIONS MUST BE MEASURED FOR FIRST ARITICAL APPROVAL.
4. ALL CRITICAL DIMENSIONS SHOWN MUST MEET A MINIMUM CPK VALUE OF 1.33.
5. ALL NON-SHOWN DIMENSION IN THE DRAWING, MUST BE TAKEN FROM 3D DATA.
6. THE DIMENSIONS NEED TO FOLLOW STANDARD DRAWING TOLERANCES TABLE AS BELOW UNLESS OTHERWISE STATED.
7. ALL PARTS MUST BE RoHS COMPLIANT.
8. PUNCH DIRECTION SHOWN.
9. ALL PARTS TO ABIDE TO FB COSMETIC AND INSPECTION GUIDELINES.
10. PLEASE REFER TO THE DRAWING WHICH DEFINE SOME SHEARED EDGES NEED TO BE COATED SILVER PEN, UNCOATED AREAS MAY HAVE THE POSSIBILITY OF RUSTING.
11. SILVER PEN TYPE: UNIPAINT PX-20 SILVER #63614 MEDIUM LINE OR ZEBRA #200M SILVER MEDIUM POINT.

ITEM	Q'Y	DESCRIPTION	SUPPLIER
1	1	RACK MOUNT BRACKET-R-V1,SGCC 1.5T	KINGDOM
2	1	CAPTIVE SCREW,33-733-290-270	FIVETECH

ZONE	DESCRIPTION
12	MODIFY THE NOTES / ADD PUNCH DIRECTION
13	ADD SILVER PEN AREA DEFINITION
,	,
,	,
,	,

Reason

This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released,or disclosed without expressed written permission.

UNSPECIFIED TOL'S (+/-0.2mm)

ANGLE +/- 1°	DIM \ GRADE	0	1	2	3	4	5
	0------16	0.05	0.1	0.15	0.2	0.2	0.5
	16------63	0.05	0.15	0.2	0.3	0.3	0.8
	63------250	0.05	0.2	0.25	0.4	0.5	1.2
	250------500	0.1	0.25	0.3	0.6	0.8	1.8
	500------1000		0.3	0.5	0.8	1.2	3.0

ROUGHNESS

FINISH.
COATING:NO
PRINTING:NO

PART NO. 123400001240A

SCALE 1/1 | UNIT MM ~~(IN)~~

DESIGN Curtis 29-JUN-16

MATERIAL SGCC T=1.5mm

facebook

DWG. TITLE. RACK MOUNT BRACKET-R-V1 SGCC ES7632BT-0415-168FB

SHEET 1/1

REV. 03

SIZE A3