





SCALE 1.000










SECTION A-A



⚠NOTES:
1. ALL DIMENSIONS SHOWN IN MILLIMETERS.
2. DIMENSIONS (1)~(5) ARE IQC CHECKPOINT.
3. ALL DIMENSIONS MUST BE MEASURED FOR FIRST ARITICAL APPROVAL.
4. ALL CRITICAL DIMENSIONS SHOWN MUST MEET A MINIMUM CPK VALUE OF 1.33.
5. ALL NON-SHOWN DIMENSION IN THE DRAWING, MUST BE TAKEN FROM 3D DATA.
6. THE DIMENSIONS NEED TO FOLLOW STANDARD DRAWING TOLERANCES TABLE AS BELOW UNLESS OTHERWISE STATED.
7. ALL PARTS MUST BE RoHS COMPLIANT.
8. ALL PARTS TO ABIDE TO FB COSMETIC AND INSPECTION GUIDELINES.

Reason	⚠	MODIFY THE NOTES.
This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released,or disclosed without expressed written permission.	,	,
	,	,
	,	,
	,	,
	ZONE	DESCRIPTION

UNSPECIFIED TOL'S (+/-0.2mm)

ANGLE +/- 1°	DIM \ GRADE	0	1	2	3	4	5
	0------16	0.05	0.1	0.15	0.2	0.2	0.5
	16------63	0.05	0.15	0.2	0.3	0.3	0.8
ROUGHNESS	63------250	0.05	0.2	0.25	0.4	0.5	1.2
	250------500	0.1	0.25	0.3	0.6	0.8	1.8
	500------1000	/	0.3	0.5	0.8	1.2	3.0

FINISH.
TRANSPARENT, HIGH POLISH

PART NO.
125400000180A

SCALE 1/1 | UNIT MM ~~EIN~~

DESIGN | Curtis | 29-MAY-16

MATERIAL
SABIC PC 945A UL94-V0

facebook

DWG. TITLE. SHEET 1/1 | REV. | SIZE

LIGHT PIPE FAN ES7632BT-0415-168FB | 02 | A3