




SCALE 2.000







NOTES:
1. DIMENSIONS (1)~(3) ARE IQC CHECKPOINT.
2. NON-SHOWN DIMENSION IN THE DRAWING, MUST BE TAKEN FROM 3D DATA.
3. REMOVE ALL OIL, BURRS, BREAK, SHARP EDGES AND CORNERS.
4. ALL MATERIAL SHOULD BE MATCH RoHS REQUEST.

Reason		
	,	,
	,	,
	,	,
	,	,
	,	,
	ZONE	DESCRIPTION

This document and the technical data disclosed are proprietary to Accton Tech. Corp. and shall not be duplicated, used, released,or disclosed without expressed written permission.

UNSPECIFIED TOL'S (+/-0.2mm)

ANGLE +/- 1°	DIM \ GRADE	0	1	2	3	4	5
ROUGHNESS	0------16	0.05	0.1	0.15	0.2	0.2	0.5
	16------63	0.05	0.15	0.2	0.3	0.3	0.8
	63------250	0.05	0.2	0.25	0.4	0.5	1.2
	250------500	0.1	0.25	0.3	0.6	0.8	1.8
	500------1000		0.3	0.5	0.8	1.2	3.0

FINISH.
COATING: NO
PRINTING: NO

PART NO. 123400001028A

SCALE 1/1 | UNIT MM ~~(IN)~~

DESIGN | Curtis | 15-DEC-14

MATERIAL
SECC T=1.0mm

Accton TECHNOLOGY CORP.

DWG. TITLE. SHEET 1/1 | REV. 01 | SIZE A3

IRON RETAINER BRACKET ES6632BT-FLF-168FB