






NOTES

- FINISH:- PAINT BLACK
- MATERIALS SPECIFIC:-STEEL, MILD, COLD-ROLLED, to EN 10130:2006 Gr.DC01
- DIMENSIONS & TOLERANCES INDICATED INCLUDE PAINT
- PAINT THICKNESS APPLIED = $0.12 \pm 10\%$
- ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- GEOMETRY:- L/H AND RIGHT COMPONENTS REQUIRED (L/H FULLY DIMENSIONED)
- RELEASE LEVEL: - ECN Production



1	ECN 9571	20/06/22	DPW		
ISS.	E.C.N. No / DESCIP	DATE	NAME	CHK'D	

THIRD ANGLE
PROJECTION.



ALL DIM'S
ARE IN MM.


Meta

MASS APPROX. 3.4 Kg


TOLERANCE UNLESS OTHERWISE
STATED ANSI STANDARD:
0.0 : ± 0.8
0.00 : ± 0.5
0.000 : ± 0.25
ANGLES : $\pm 1.0^\circ$

(CRITICAL DIMENSION)

SCALE 0.15 @ A3	
MATERIAL MILD STEEL DC01 1.2 THK	
DESCRIPTION	O.C.P. V3 META
PROFILE CABLE MNG' L/H PNT	
PROFILE CABLE MNG' R/H PNT	
DWG No	C29054_LH
	C29054_RH
1	1 OF 2



DETAIL A
SCALE 0.700



BRIDGE FORM DETAIL H
SCALE 1.0

SCALE	0.15 @ A3	
MATERIAL	MILD_STEEL_DC01	
DESCRIPTION	O.C.P. V3	META
PROFILE CABLE MNG' L/H SM		
DWG No	C29054_LH	ISS.
		2
DRAWING SHEET 2 OF 2		