








NOTES

- FINISH:- PAINT BLACK
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
- REFERENCE DRAWINGS: - Na.
- ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- ALL GEOMETRICAL TOLERANCES CONSIDERED "CRITICAL" CP= 1.33. BASIC DIMENSIONS ARE CONTAINED IN A RECTANGULAR BOX . WITH THE TOLERANCE RANGE DEFINED IN THE ASSOCIATED GEOMETRICAL TOLERANCE.
- WELDING
 - ALL WELDING DIMENSIONS ARE MINIMAL REQUIREMENTS (UNLESS OTHERWISE STATED).
 - WELDING SYMBOLS TO BS EN ISO 2553.
- RELEASE LEVEL: - ECN Production

DIMENSIONS CONTAINED IN AN OBROUND REQUIRE A CP OF 1.33

ISS.	E.C.N. No / DESCRIP	DATE	NAME	CHK'D
1	ECN 9571	17/06/22	P.C	

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 6.1 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.25 @ A3

MATERIAL MILD_STEEL_DC01 3.0 THK'

DESCRIPTION O.C.P. v3 | META

PLATE BASE TRAY STIFFENING PNT

DWG No C29998

1

1 OF 1