






		1	2	3	4	5	6	7
A	16	2	TUBULAR HANDLE (KIP No K0237.12805)					
	15	2	T.S.F. NUTSERT BOLLHÖFF 23317080300 M8	430911	23317080300			
	14	4	STABILISER PAINT PROTECTION BLOCK LOWER	0	C29504			
	13	2	STABILISER PAINT PROTECTION BLOCK	0	C29490			
	12	1	STABILISER OCP PNT	0	C29485_PNT			
	11	2	STABILISER MUSHROOM	0	C29492			
	10	1	SEPARATOR PLUNGER	0	C29620			
	9	8	SCREW, TAPTITE PN HD, POZI, M6x10, Z/P, DIN 7500	425888	425888			
	8	2	M8 X 20 X 1.25p SOC HD CAP SCREW DIN 912	0	D0208106			
	7	8	M6 X 16 X 1.0p SOC HD CAP SCREW DIN 912	0	D0215291			
	6	2	LABEL NO LIFT POINT	0	LABEL_DO_NO_LIFT			
	5	1	LABEL GREEN PLUNGER	0	C31778			
	4	2	LABEL GREEN HANDLE	0	C31779			
	3	1	INDEXING PLUNGER (Kipp P/N K0630.24308)		K0630-24308			
	2	2	CASTOR WHEEL & ROLLER BEARING (ALGOOD W-54260-RX-RB-12MM)	400116	400116			
	1	2	AXLE & NUT KIT ALGOOD HEAT TREATED (ALGOOD AN-54263-120HT)	426259	426259			
B	ITEM	QTY	DESCRIPTION	PART No.	DRWG No.			
	BILL OF MATERIALS							



SCALE 0.200



SCALE 0.200



- NOTES
- SECURE ALL FIXINGS TO 5NM +/-10% UNLESS STATED OTHERWISE
 - DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
 - SHARP EDGES & BURRS: ALL EDGES MUST CONFORM TO ULI439.
 - THREAD DIMENSIONS CONFORM TO ISO METRIC STANDARD UNLESS OTHERWISE SPECIFIED
 - RELEASE LEVEL: - Concept

DIMENSIONS CONTAINED
IN AN OBOUND REQUIRE
A CP OF 1.33

F	UPDATE	12/01/22	P.C.		
ISS.	E.C.N. No / DESCIP	DATE	NAME	CHK'D	

	SCALE 0.20 @ A3	
	MATERIAL VARIOUS	
THIRD ANGLE PROJECTION.	MASS APPROX.	8.5 Kg
	TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:	
	0.0 : ±0.8	
	0.00 : ±0.5	
ALL DIM'S ARE IN MM.	0.000 : ±0.25	
	ANGLES : ±1.0°	
CRITICAL DIMENSION		
DESCRIPTION		v3 O.C.P.
STABILISER ORV3 ASM		
DWG No		C29489
		F
		1 OF 1