


NOTES

- ALL GEOMETRICAL TOLERANCES CONSIDERED "CRITICAL" CP = 1.33. BASIC DIMENSIONS ARE CONTAINED IN A RECTANGULAR BOX WITH THE TOLERANCE RANGE DEFINED IN THE ASSOCIATED GEOMETRICAL TOLERANCE.
- GEOMETRY:- L/H AND RIGHT COMPONENTS REQUIRED (R/H FULLY DIMENSIONED)
- FINISH:- Z/P 38µ TARGET THK'NES
- FINISHED COMPONENTS (PAINTED, PLATED, RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- ° HIGHLIGHTED EDGES REQUIRE SECONDARY DE-BURRING OPERATION, BUILT INTO HARD-TOOL, OR MANUAL POST PIERCE DE-BURRING OPERATION.
- MATERIALS (SPECIFIC): -STEEL, METALLIC COATED DX51D, Z/P 275g/m² (19µ LAYER) to EN 10346. QUALITY A.
 YOUNGS MODULUS: 200GPa±20GPa
 POISSONS RATIO: 0.27-0.3
 MIN.YIELD STRENGTH : 140MPa
- RELEASE LEVEL: - Concept

° END EDGES PER RAIL TO HAVE ADDITIONAL DE-BURRING OPERATION, ENSURING ANY BURR IS FULLY REMOVED. (BOTH RAILS)

DIMENSIONS CONTAINED IN AN OBROUND REQUIRE A CP OF 1.33

ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
2	1	SHELF POWER LH 10U SM	433173	C32621_LH
1	1	LEVER SHELF RELEASE SPRING CLIP v2 SM	433164	C32615

BILL OF MATERIALS

ISS.	E.C.N. No / DESCRIP.	DATE	NAME	CHK'D
2	UPDATE	12/04/22	S.S.	

Meta

THIRD ANGLE PROJECTION.

MASS APPROX. 0.7 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 ± 0.8
0.00 ± 0.5
0.000 ± 0.25
ANGLES ± 1.0°

ALL DIM'S ARE IN MM.

CRITICAL DIMENSION

SCALE 0.25 @ A3

MATERIAL STEEL_METALLIC_COATED_DX51D_275 2.0 THK'

DESCRIPTION O.C.P. V3 FACEBOOK

SHELF POWER LH 10U SM
SHELF POWER RH 10U SM

DWG No C32621_LH
C32621_RH

2

1 OF 1