

























NOTES
- FINISH:- PAINTED
- REFERENCE DRAWINGS: - Na
- DIMENSIONS AND TOLERANCES INDICATED INCLUDE PAINT THICKNESS OF 0.12±10%
- ALL CRITICAL DIMENSIONS CP=> 1.33
- REFER TO 3D CAD MODEL FOR WELD LOCATION DEFINITON
- SHARP EDGES & BURRS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.
- ALL WELDING DIMENSIONS ARE MINIMAL REQUIRMENTS (UNLESS OTHERWISE STATED).
- WELDING SYMBOLS TO BS EN ISO 2553.
- RELEASE LEVEL: - Concept

ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
4	2	YOKE, CASTOR, FIXED BOLT ON	437911	C29319
3	2	STABILISER SIDE BRACE SM	0	C29486
2	1	STABILISER JOINING PLATE SM	0	C29483
1	2	STABILISER CASTOR PLATE SM	0	C29481

BILL OF MATERIALS

ISS.	E.C.N. No / DESCRIP	DATE	NAME	CHK'D
D	UPDATE	19/11/21	P.C.	

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 6.1 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSi STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.15 @ A3

MATERIAL VARIOUS

DESCRIPTION ORV3 | OCP

STABILISER OCP PNT

DWG No C29485

D

1 OF 1