NOTES

1. MATERIAL: MULTIPLE
   FINISH: RAW

2. TOLERANCES ADDED TO DRAWING DIMENSIONS TAKE PRECEDENCE OVER OTHER TOLERANCES. DIMENSIONS MARKED CTF WILL BE MEASURED DURING CpK.


3. - UNFINISHED (SHEET METAL / RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS ACCORDING TO ISO 13715


4. WELD SYMBOLS TO ISO 2553 UNLESS OTHERWISE STATED

5. ALL WELD LENGTH TOLERANCES +5/-0mm UNLESS OTHERWISE STATED
   ALL WELD HEIGHTS TO ISO 5817 UNLESS OTHERWISE STATED
   WELD LENGTH MEASUREMENTS TO BE TAKEN FROM START/FINISH OF COMPLETE WELD


6. REFERENCE DRAWINGS: Na


REV.	CHANGE	ECN	DATE	NAME	ZONE
A	CREATED	-	17/02/26	J.G.	-






SCALE 0.250







ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
2	1	PLATE REAR MIDDLE FOOT 2 INNER SM	402906	C37348
1	1	FOOT REAR MID 154MM HIGH 2 SM	402905	C37070

BILL OF MATERIALS FOR REAR MIDDLE FOOT 154MM HIGH LABEL 2 WLD PART NO. 402904

Meta

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 2.5 Kg

FOR UNSPECIFIED DIMENSIONS REFER TO 3D CAD. UNDIMENSIONED FEATURES TO BE INTERPRETED FROM 3D CAD FILE AND TOLERANCES FROM TOL. TABLE
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.40 @ A3

MATERIAL [.1] THK'

DESCRIPTION AQUATRON META

REAR MIDDLE FOOT 154MM HIGH LABEL 2 WLD

DWG No C37069_WLD

A

1 OF 1