NOTES

1. MATERIAL: MULTIPLE
   FINISH: RAW

2. TOLERANCES ADDED TO DRAWING DIMENSIONS TAKE PRECEDENCE OVER OTHER TOLERANCES. DIMENSIONS MARKED CTF WILL BE MEASURED DURING CpK.


3. - UNFINISHED (SHEET METAL / RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS ACCORDING TO ISO 13715


4. WELD SYMBOLS TO ISO 2553 UNLESS OTHERWISE STATED

5. ALL WELD LENGTH TOLERANCES +5/-0mm UNLESS OTHERWISE STATED
   ALL WELD HEIGHTS TO ISO 5817 UNLESS OTHERWISE STATED
   WELD LENGTH MEASUREMENTS TO BE TAKEN FROM START/FINISH OF COMPLETE WELD


6. REFERENCE DRAWINGS: Na

REV.	CHANGE	ECN	DATE	NAME	ZONE
A	INITIAL RELEASE	-	15/09/25	GAB	-







SCALE 0.250




SCALE 0.250




SECTION Z - Z





SECTION Y - Y



ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
2	1	FOOT CORNER 154MM HIGH 2 SM	402908	C37071
1	1	CORNER FOOT INNER LABELLED 2PLATE	402909	C37193

BILL OF MATERIALS FOR CORNER FOOT 154MM HIGH LABELLED 2 WLD PART NO. 402907

Meta

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 2.0 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.50 @ A3

MATERIAL: MULTIPLE_MATERIALS

DESCRIPTION: AQUATRON | META

CORNER FOOT 154MM HIGH LABELLED 2 WLD

DWG No: C37072_WLD

A

1 OF 1