REV.	CHANGE	ECN	DATE	NAME	ZONE
A	DRAWN	-	17/02/26	DG	

NOTES


1. MATERIAL: STEEL, MILD, COLD-ROLLED, to EN 10130:2006 Gr.DC01 1.2mm THK
   FINISH: RAW


2. TOLERANCES ADDED TO DRAWING DIMENSIONS TAKE PRECEDENCE OVER OTHER TOLERANCES. DIMENSIONS MARKED CRITICAL OR PROCESS WILL BE MEASURED DURING CpK.

3. FINISHED COMPONENTS (PAINTED, PLATED, RAW) PARTS: ALL EDGES SHALL BE CONDITIONED FOR HANDLING WITH BURRS NO GREATER THAN 10% MATERIAL THICKNESS, ACCORDING TO ISO 13715, AND MUST CONFORM TO UL 1439.

[4] SECURE INSERT I.A.W. MANUFACTURERS INSTALLATION INSTRUCTIONS

5. REFERENCE DRAWINGS: No





2	1	SLEEVE FRONT CABLE MANAGER PNT	402945	C37350_PNT
1	1	PRESS-IN PLNGR (SOUTHCo 56-161-059)	405018	56-161-059
ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
BILL OF MATERIALS FOR SLEEVE FRONT CABLE MANAGER PEM PART NO. 402944				

	1	SLEEVE FRONT CABLE MANAGER SM	402946	C37350
	AS REQUIRED	PAINT, RAL 9005, TEXT (CARBON BLACK)	406087	406087
	AS REQUIRED	PAINT RAL9005 2 PART DIP MIX	478517	478517_
ITEM	QTY	DESCRIPTION	PART No.	DRWG No.
BILL OF MATERIALS FOR SLEEVE FRONT CABLE MANAGER PNT PART NO. 402945				

FEATURES WITHOUT TOLERANCES SHALL USE THE FOLLOWING TABLE:		SOFT TOOL TOLERANCE TABLE					
FEATURE TYPE TABLE		DIM. VALUE (X)					
#	TYPE	0 < X < 25	25 < X < 125	125 < X < 250	250 < X < 375	375 < X < 500	500 < X
1	Feature to feature (same operation)	0.13	0.13	0.18	0.18	0.25	0.38
2	Feature to feature (different operation)	0.25	0.30	0.30	0.38	0.38	0.51
3	Blank cutouts	0.10	0.13	0.18	0.30	0.38	0.51
4	Bend to cutout	0.30	0.30	0.30	0.38	0.38	0.51
5	Bend to bend or cuts w/bend between (same op)	0.30	0.38	0.38	0.51	0.51	0.64
6	Bend to bend (different operation)	0.38	0.38	0.38	0.38	0.51	0.64

1±0.12

Meta

THIRD ANGLE PROJECTION.

ALL DIM'S ARE IN MM.

MASS APPROX. 0.3 Kg

TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD:
0.0 : ±0.8
0.00 : ±0.5
0.000 : ±0.25
ANGLES : ±1.0°

CRITICAL DIMENSION

SCALE 0.50 @ A3

MATERIAL MILD_STEEL_DC01 1.2mm THK

DESCRIPTION AQUATRON | META

SLEEVE FRONT CABLE MANAGER SM

DWG No C37350

A

1 OF 1