

	OCP Ready v2 for Hyperscale Data Center Site Assessment	PDG TY1-DC1			
	Self Assessment Status:	COMPLETE-MEETS REQUIREMENTS			
	Data Center Location Name	PDG TY1			
	Data Center Location Address	2-1917 Nissincho, Kita-ku, Saitama City, Saitama Prefecture, Japan			
	Site Development Category:	1. Multi-tenant Capacity Available	04/24/2025	24MW completed and operational. Another 24MW under construction.	
	Site Description: IT Technical Space (White Space) Area	12,096 m2 (378/DC Hall x 8 Halls x 4 Floors)			
	Site Description: Critical IT Power	48 MW IT power			
	Site Description: Network Provider Availability	Carrier neutral. Currently 4 carriers are ready to bring fibre into the DC. 4 point of entry onsite			
	Site Description: Facility Features	Active Stand by 66kV power from TEPCO, Generator powers total building load, Air Cooled Chillers, Chilled water to DC Halls			
	Site Description: Other Services	Manned 24x365 by trained facilities engineers, 24 x 365 Security on duty			
	Date Original Assessment is Completed	01/31/2025			
	Re-Assessment Date:	08/31/2026			
Ref:	REQUIREMENTS - Attribute (Must have an Optimum or Acceptable result)	Parameter	Result	Notes/ Actual Parameters	
1	CAMPUS SITE ACCESS & LOGISTICS				
1.0	SITE ACCESS				
1.0-A	Vehicular Access inc. truck circulation	1. Roadway access to loading dock to allow for a trailer 12.2m (40') Wheelbase	Optimum		
1.0-B	Building Access	1. Covered loading dock with leveler	Optimum		
1.0-C	Delivery pathway, Loading dock to storage room	1. ≥ 2.75m (108in) H x ≥ 1.6m (63in) W unobstructed access and threshold free	Optimum		
1.0-D	Delivery pathway, Goods in to IT Technical Space	1. ≥ 2.75m (108in) H x ≥ 1.6m (63in) W unobstructed access and threshold free	Optimum		
1.0-E	Corridor floor rolling load	1. ≥680 kg (1500 lb/ft2) (6.67 kN) slab on grade	Optimum		
1.0-F	Unboxing/pre-staging/storage area floor uniform load	1. ≥1221 kg/m2 (250 lb/ft2) (11.97 kN/m2) slab on grade	Optimum		
1.0-G	Unboxing/pre-staging/storage area floor concentrated load	1. ≥680 kg (1500 lb/ft2) (6.67 kN) slab on grade	Optimum		
1.1	ACCESS CONTROLS & MONITORING				
1.1-A	Site perimeter fence	2. ≥2.43m (96in) anti-climb fence	Acceptable		
1.1-B	Site security lighting	1. Site lighting with backup power	Optimum		
1.1-C	Main Security Checkpoint (or check in location)	1. Staffed 24/7	Optimum		
1.1-D	Levels of security to gain access to IT Technical Space	1. >3 (site perimeter, building perimeter, secure corridor and IT Technical Space)	Optimum		
1.1-E	Video surveillance data record archive	1. >30 days	Optimum	90 days	
1.1-F	Visitor access requirements	1. Pre-approved with valid government issued ID and escorted	Optimum		
1.1-G	Entrance and exit door monitoring	1. All entrance and exit doors are electronically monitored and recorded	Optimum		
1.2	RAMPS				
1.2-A	Gradient	1. Not Applicable - No Ramps Required	Optimum		
1.2-B	Length	1. Not Applicable - No Ramps Required	Optimum		
1.2-C	Width	1. Not Applicable - No Ramps Required	Optimum		
1.2-D	Landing area	1. Not Applicable - No Ramps Required	Optimum		
1.2-E	Railings	1. Not Applicable - No Railings Required	Optimum		
1.3	FREIGHT LIFTS / ELEVATORS				
1.3-A	Weight loading	1. ≥3000kg (6600lbs)	Optimum		
1.3-B	Door height	1. ≥2.75m (108in) Lift /Elevator door opening height (internal cabin)	Optimum		
1.3-C	Width	1. ≥1.8m (71in) Unobstructed door opening width	Optimum		
1.3-D	Depth	1. ≥3.4m (134in) Unobstructed cabin depth	Optimum		
2	IT TECHNICAL SPACE (WHITE SPACE)				
2.0	STRUCTURAL				
2.0-A	Floor rolling load	1. ≥680kg (1500lb) (6.67kN) slab on grade	Optimum		
2.0-B	Floor uniform load	1. ≥1221 kg/m2 (250 lb/ft2) (11.97 kN/m2) slab on grade	Optimum		
2.0-C	Floor concentrated load	1. ≥680kg (1500lb) (6.67kN) slab on grade	Optimum		
2.0-D	Finished floor to ceiling height	2. ≥3.65m (144in) clear space (no obstructions)	Acceptable		
2.0-E	Access floor	1. CFD study available to view on request (if used for cooling)	Optimum		
2.1	ELECTRICAL				
2.1-A	Class Rating	1. 3 (e.g. Bicsi F3 or UTI Tier 3 Notes Required)	Optimum	Designed to UTI III	
2.1-B	Row level diverse power feeds	1. 2N (A+B)	Optimum	Distributed Redundant 4 to make 3	

2.1-C	Nominal circuit capacity	1. 1ϕ and 3ϕ circuits available based on customer requirements (e.g. 1ϕ 230-240V, 3ϕ 400V-415V Notes Required)		Optimum	32A 400/230VAC
2.1-D	Circuit frequency	1. 47-63 Hz		Optimum	
2.1-E	Power receptacle / WIP Type	1. All power receptacle types supported		Optimum	
2.1-F	Circuit receptacle location	1. All circuit receptacle locations supported		Optimum	
2.1-G	Upstream UPS options	1. N+N UPS feed		Optimum	Distributed Redundant 4 to make 3
2.1-H	Rack-based batteries permitted	1. Allowed		Optimum	
2.1-I	Generator load acceptance time	2. >35 seconds (Notes Required)		Acceptable	40sec, Parallel generator system
2.2	COOLING				
2.2-A	Class Rating	1. 3 (e.g. Bicsi F3 or UTI Tier 3 Notes Required)		Optimum	Designed to UTI III
2.2-B	Supplemental Advanced Cooling	1. Not Applicable		Optimum	
2.2-C	Rack airflow direction	1. Front to Back		Optimum	
2.2-D	Air containment methods	2. Cold aisle containment		Acceptable	
2.2-E	Maximum rack density	1. ≥12kW		Optimum	
2.2-F	Minimum cold aisle width	1. ≥1400mm (56in)		Optimum	
2.2-G	Minimum free width cold aisle (Inside cage)	1.≥1400mm (56in)		Optimum	
2.2-H	Minimum hot aisle width	1. ≥1200mm (48in)		Optimum	
2.2-I	Inlet air conditions	1. ASHRAE Recommended		Optimum	
2.2-J	Air quality	1. MERV 8 filters on outside air		Optimum	MERV13 filter
2.2-K	Temperature rise	1. ≥12 Deg C DeltaT		Optimum	
2.2-L	Cabinet blanking of open space	1. Mandatory		Optimum	
3	TELECOMMUNICATIONS				
3.1	ACCESS PROVIDERS AND OUTSIDE PLANT (OSP) Fiber				
3.1-A	OSP fiber to data center campus	1. 3 diverse OSP entrances to the data center campus		Optimum	
3.1-B	Carriers and backbone providers	1. Carrier neutral with expansion capability (Notes Required)		Optimum	
3.2	MEET-ME ROOMS (MMRS)				
3.2-A	Number and Location	1. N+N Isolated MMRS with dedicated OSP fiber entrance from service providers		Optimum	
3.3	MMR CABLING				
3.3-A	MMR to IT Technical Space Pathways	1. 2 dedicated diverse pathways from 2 MMRS		Optimum	
3.3-B	MMR to IT Technical Space Conduit Pathway sizing	1. ≥100mm (4in) conduit pathways		Optimum	
3.4	MMR ELECTRICAL				
3.4-A	Class Rating	1. 3 (e.g. Bicsi F3 or UTI Tier 3 Notes Required)		Optimum	Designed to UTI III
3.4-B	Row level diverse power feeds	1. 2N (A+B)		Optimum	Up to 4 diverse feed per rack
3.4-C	Nominal circuit capacity	1. 1ϕ and 3ϕ circuits available based on customer requirements (e.g. 1ϕ 230-240V, 3ϕ 400V-415V Notes Required)		Optimum	32A 400/230VAC
3.4-D	Circuit frequency	1. 47-63 Hz		Optimum	50 Hz
3.4-E	Upstream UPS options	1. UPS systems derived from an isolated house lineup		Optimum	IT-UPS, Mech-UPS and BMS-UPS are separated out.
3.4-F	UPS Redundancy	1. N+1		Optimum	Distributed Redundant 4 to make 3
3.4-G	Generator load acceptance time	2. >35 seconds (Notes Required)		Acceptable	40sec, Parallel generator system
3.5	MMR COOLING				
3.5-A	MMR cooling redundancy per room	2. N+1		Acceptable	
3.5-B	MMR cooling system type	2. Chilled water		Acceptable	CRAH
3.5-C	MMR cooling isolation	1. Isolated from IT technical space cooling system		Optimum	
3.6	MMR ACCESS CONTROLS				
3.6-A	Customer access to MMR(s)	1. Controlled by the colocation data center and escorted		Optimum	
3.6-B	Service Provider access to MMR(s)	1. Controlled by the colocation data center and escorted		Optimum	
3.6-C	Biometric readers, badge readers, and video surveillance installed for the MMR(s)?	1. Yes		Optimum	
4	SERVICE				
4.1	OPERATIONS AND SPARE PARTS				

4.1-A	Critical spares program	1. On hand spares available on campus	Optimum	
4.1-B	Critical Response SLA	1. Yes	Optimum	
4.1-C	Remote hands program	1. Yes	Optimum	
4.1-D	Office Space	1. Dedicated space available for fitout	Optimum	
5	EFFICIENCY			
5.0-A	Site Operations Standards	1. OCP Critical Facility Operations Guidelines	Optimum	
5.0-B	Operational Sourcing Standard	1. Integrated options	Optimum	
5.0-C	Work Note Communication and Coordination	1. Yes (e.g. Dedicated portal, Teams, Sharepoint)	Optimum	
5.0-D	Site PUE Monitoring	1. Continuously monitored	Optimum	PUE is monitored by BMS
5.0-E	Site Design PUE at Full Load	2. >1.3 @ 80% Max Utilization (e.g. due to location in Ashrae Climate zone OA, notes required for PUE calculation)	Acceptable	
5.0-F	Site Annualized PUE Current Achievement	2. Other (Notes required)	Acceptable	Handover completed in Aug 2025; currently in tenant IT equipment load ramp-up phase. Steady-state PUE evaluation will be reported upon reaching stable operational load.
5.0-G	Site WUE Monitoring	1. Not applicable (e.g. zero water requirement)	Optimum	
5.0-H	Site CUE Monitoring	1. Continuously monitored	Optimum	
6	OPENNESS			
6.0-A	PUE Published	2. Other (Notes Required)	Acceptable	Available on Request
6.0-B	Facility Design Drawings & Files	1. Available to view upon request	Optimum	
6.0-C	BMS / PMS Customer Access	1. External access provided through a MQTT Broker or other air gapped connection for telemetry purposes. (e.g. power monitoring)	Optimum	
7	CERTIFICATIONS			
7.0-A	ISO/IEC 27001	1. Certification in process	Optimum	Updated
7.0-B	SOC 1 Type II	1. Certification available on request	Optimum	
7.0-C	SOC 2 Type II	1. Certification in process	Optimum	Updated
7.0-D	PCI-DSS	1. Certification available on request	Optimum	
7.0-E	Sustainability Assessment	1. LEED Certification achieved	Optimum	LEED V4 ID+C: Gold certificate
7.0-F	Data Center Certification	2. Other (Notes Required)	Acceptable	NVIDIA DGX-Ready Data Center for liquid cooling certificate
	Site Assessment Version - v1.0 rev1.15			